



Grand L 3240 Compact Tractors

Grand L 40 Series Competitive Comparison

MODEL		Kubota L3240		John Deere 3320		New Holland Boomer 30			
		Gear 2WD/4WD	HST 4WD	Gear	HST 4WD	Gear 4WD	HST 4WD		
Engine	Engine gross power	HP	34		32.5		28.1		
	PTO power	HP	26.5	25	25.5	25	23.9	22.5	
	No. of cylinders		3		3		4		
	Total displacement	cu.in.	100.5		100		92		
	Rated revolution		2700		2600		2600		
	Aspiration		Natural		Natural		Natural		
	Fuel tank capacity	gal.	11.6		11.8		8.7		
	Double air cleaner		Standard		N/A		Standard		
Drive train	Transmission		DT/GST	HST PLUS	Gear	HST	Gear	HST	
	Stall Guard		N/A	YES	N/A	YES	N/A	N/A	
	Hydro Dual Speed		N/A	YES	N/A	NO	N/A	N/A	
	HST Response Control		N/A	YES	N/A	YES	N/A	N/A	
	Auto Throttle		N/A	YES	N/A	No	N/A	N/A	
	Transmission Gear Ranges		Std. DT- 8F/8R GST- 12F/8R	3-Range With Hydro Dual Speed Infinitely Variable		12F/12R	3 Range Infinitely Variable	12Fx12R Synchro Shuttle Shift	3 Range Infinitely Variable
	Max. traveling speed	mph	16.5	15.8	16.4		14.2	14.8	
	Brake		Multi-plate wet disc		Multi-plate wet disc		Wet, Multi, Disc		
PTO clutch		DT/GST- Hyd. Clutch	Master & Hyd. Clutch		Multi-disc, wet				
Tires	Farm	Front	2WD: 6-16 4WD: 7.2-16		7-14		7x14		
		Rear	2WD: 12.4-24 4WD: 12.4-24		11.2-24		11.2x24		
	Turf	Front	27 x 8.50 - 15		27 x 8.50 - 15		25.8.50-14		
		Rear	355 / 80 - 20		41 x 14 - 20		41x14.00-20		
	R4	Front	2WD: N/A 4WD: 10 - 16.5		25 x 8.50 - 14		25x8.50-14		
		Rear	2WD: N/A 4WD: 420 / 70 - 24		15 - 19.5		43x16-20		
Hydraulic System	Implement Pump capacity	gpm	8.3		8.6		8.2		
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2646		2200		1433		
	Front Loader valve & lever		Standard		Standard		Optional		
	Power steering		Standard		Standard		Standard		
Others	Factory Cab Option		N/A	Optional	N/A	N/A	N/A	N/A	
	Cruise Control		N/A	Standard	N/P		Standard		
Dimensions	Wheelbase	in.	2WD: 71.3 / 4WD: 71.7		68		66		
	Tread	Front	in. F: 47.6 / DT: 51.6 / GST: 55.5 / HST: 59.4		N/P		N/P		
		Rear	in. F: 47.2 / DT: 51.2 / GST: 54.5 / HST: 58.3		N/P		N/P		
	Overall Length w/ 3-Point Hitch	in.	128.5		120.2		119		
	Overall Height to top of ROPS	in.	97		93.3		91		
	Overall Width (min. tread)	in.	N/P		68.4		N/P		
	Min. ground clearance	in.	14		10.9		N/P		
	Min. turning radius w/ brake	ft.	8.9		8.8		N/P		
Weight (w/ ROPS)	lbs.	F: 3153 / DT: 3252 / GST: 3296 / HST: 3395		2900		3121			

N/A = Not Available N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge.

Kubota reserves the right to change the specifications relating to its products without notice.



Grand L 3540 Compact Tractors

Grand L 40 Series Competitive Comparison								
MODEL		Kubota L3540		John Deere 3520		New Holland Boomer 35		
		Gear 4WD	HST 4WD	Gear	HST 4WD	Gear 4WD	HST 4WD	
Engine	Engine gross power	HP	37		37.1		38	
	PTO power	HP	29.5	28	30.5	30.0	32.2	30.3
	No. of cylinders		3		3		4	
	Total displacement	cu.in.	111.4		91.5		107	
	Rated revolution		2700		2600		2700	
	Aspiration		Natural		Turbocharged		Natural	
	Fuel tank capacity	gal.	11.6		11.8		8.7	
	Double air cleaner		Standard		N/A		N/P	
Drive train	Transmission		GST	HST PLUS	Gear	HST	Gear	HST
	Stall Guard		N/A	YES	N/A	YES	N/A	N/A
	Hydro Dual Speed		N/A	YES	N/A	NO	N/A	N/A
	HST Response Control		N/A	YES	N/A	YES	N/A	N/A
	Auto Throttle		N/A	YES	N/A	ROPS Auto HST Only	N/A	N/A
	Transmission Gear Ranges		12F/8R	3-Range With Hydro Dual Speed Infinitely Variable	12F/12R	3 Range Infinitely Variable	12Fx12R Synchro Shuttle Shift	3 Range Infinitely Variable
	Max. traveling speed	mph	16.5	15.8	16.4	19	14.8	15.4
	Brake		Multi-plate wet disc		Wet Disc		Wet, Multi Disc	
PTO clutch		Master & Hyd. Clutch		Multi-disc, wet		N/P		
Tires	Farm	Front	7.2 - 16		7-14		7x14	
		Rear	12.4 - 24		11.2-24		11.2x24	
	Turf	Front	27 x 8.5 - 15		25/10.50LL-15		25.8.50-14	
		Rear	355 / 80 - 20		41LLx18-16.1		41x14.00-20	
	R4	Front	10 - 16.5		27 x 8.50 - 15		25x8.50-14	
		Rear	420 / 70 - 24		43 x 16 - 20		43x16-20	
Hydraulic System	Implement Pump capacity	gpm	8.3		8.6		8.6	
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2646		2200		1433	
	Front Loader valve & lever		Standard		Standard		Optional	
	Power steering		Standard		Standard		Standard	
Others	Factory Cab Option		N/A	Optional	N/A	N/A	N/A	N/A
	Cruise Control		N/A	Standard	N/A	N/A	N/A	N/A
Dimensions	Wheelbase	in.	71.7		68		66	
	Tread	Front	43.9		45.2		N/P	
		Rear	GST: 47.2 / HST: 51.2		N/P		N/P	
	Overall Length w/ 3-Point Hitch	in.	124.4		120.2		119	
	Overall Height to top of ROPS	in.	97		93.3		91	
	Overall Width (min. tread)	in.	N/P		52.4		N/P	
	Min. ground clearance	in.	14		10.9		N/P	
	Min. turning radius w/ brake	ft.	8.9		8.8		N/P	
Weight (w/ ROPS)	lbs.	GST: 3296		2900		3200		

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.



Grand L 3940 Compact Tractors

Grand L 40 Series Competitive Comparison											
MODEL			Kubota L3940		John Deere 3520		John Deere 3720	John Deere 4120		New Holland Boomer 40	
			Gear 4WD	HST 4WD	Gear	HST 4WD	HST 4WD	Gear	HST 4WD	Gear 4WD	HST 4WD
Engine	Engine gross power	HP	40.5		37.1		43.2	43		41	
	PTO power	HP	33	31.5	30.5	30.0	35	35.5	35	31	29
	No. of cylinders		4		3		3	4		4	
	Total displacement	cu.in.	122		91.5		91.5	148.9		153	
	Rated revolution		2700		2600		2600	2400		2600	
	Aspiration		Natural		Turbocharged		Turbo-charged	Turbo-charged		Natural	
	Fuel tank capacity	gal.	13.2		ROPS - 11.8 CAB - 13.5		ROPS - 11.8 CAB - 13.5	14.5		9.5	
	Double air cleaner		Standard		N/A		Standard	N/A		Standard	
Drive train	Transmission		DT/GST	HST PLUS	Gear	HST	HST	Gear	HST	Gear	HST
	Stall Guard		N/A	YES	N/A	YES	YES	N/A	YES	N/A	N/A
	Hydro Dual Speed		N/A	YES	N/A	NO	NO	N/A	NO	N/A	N/A
	HST Response Control		N/A	YES	N/A	YES	YES	N/A	YES	N/A	N/A
	Auto Throttle		N/A	YES	N/A	ROPS Auto HST Only	ROPS Auto HST Only	N/A	YES	N/A	N/A
	Transmission Gear Ranges		12F/8R	3 Range With Hydro Dual Speed Infinitely Variable	12F/12R	3 Range Infinitely Variable	3 Range Infinitely Variable	12F/12R	3 Range Infinitely Variable	12Fx12R Synchro Shuttle Shift	3 Range Infinitely Variable
	Max. traveling speed	mph	16.5	15.8	16.4	19	18.5	17.3	16.9	15.2	14.1
	Brake		Multi-plate wet disc		Wet Disc		Wet disc	Wet Disc		Wet, Multi Disc	
PTO clutch		DT/GST- Hyd. Clutch	Master & Hyd. Clutch	Multi-disc, wet		Multi-disk, wet	Multi Disc, Wet		N/P		
Tires	Farm	Front	8.3 - 16		7-14		7.00-14 6PR	8-16		9.5x16	
		Rear	14.9 - 24		11.2-24		11.2-24 6PR	13.6-28		13.6-24	
	Turf	Front	29 x 12.50 - 15		25/10.50LL-15		27x8.50-15 6PR	27 x 12 - 15		29x12.50-15	
		Rear	44 x 18 - 20		41LLx18-16.1		41x14.00-20	22.5 - 16.1		41x14.00-20	
	R4	Front	10 - 16.5		27 x 8.50 - 15		25x8.50-14 6PR R4	10-16.5		10x16.5	
		Rear	17.5 - 24		43 x 16 - 20		15.00-19.5	17.5-24		43x16.00-20	
Hydraulic System	Implement Pump capacity	gpm	9.8		8.6		8.6	12		8.2	
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2756		2200		2200	2500		2469	
	Front Loader valve & lever		Standard		Standard		Standard	Standard		Standard	
	Power steering		Standard		Standard		Standard	Standard		Standard	
Others	Factory Cab Option		N/A	Optional			N/A	N/A	N/A	N/A	
	Cruise Control		N/A	Standard	N/A	Optional	Standard	N/P		Standard	
Dimensions	Wheelbase	in.	74.6		68		68	71.5		69	
	Tread	Front	45.5		45.2		N/P	N/P		N/P	
		Rear	DT: 50.6 / GST: 56.5 / HST: 60.2		N/P		N/P	N/P		N/P	
	Overall Length w/ 3-Point Hitch	in.	129.5		120.2		120.2	128.2		121	
	Overall Height to top of ROPS	in.	97.4		93.3		93.3	97.2		96	
	Overall Width (min. tread)	in.	N/P		52.4		52.4	65.6		N/P	
	Min. ground clearance	in.	14.6		10.9		N/P	N/P		N/P	
	Min. turning radius w/ brake	ft.	8.9		8.8		8.8	9.2		N/P	
Weight (w/ ROPS)	lbs.	DT: 3483 / GST: 3527 / HST: 3516		2900		2900 (1316)	3700 (1679)		3200		

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the



Grand L4240 Compact Tractors

Grand L 40 Series Competitive Comparison								
MODEL		Kubota L4240		John Deere 3720	John Deere 4120		New Holland Boomer 50	
		Gear 4WD	HST 4WD	HST 4WD	Gear 4WD	HST 4WD	Gear 4WD	HST 4WD
Engine	Engine gross power	HP	44		43.2	43		47
	PTO power	HP	36.5	35	35	37.0	35	39.4 37.1
	No. of cylinders		4		3	4		4
	Total displacement	cu.in.	134.1		91.5	148.9		153
	Rated revolution		2700		2600	2400		2600
	Aspiration		Natural		Turbo-charged	Turbo-charged		Natural
	Fuel tank capacity	gal.	13.2		ROPS - 11.8 ROPS, CAB - 13.5	14.5		9.5
	Double air cleaner		Standard		Standard	N/A		Standard
Drive train	Transmission		DT/GST	HST PLUS	HST	Gear	HST	Gear HST
	Stall Guard		N/A	YES	YES	N/A	YES	N/A N/A
	Hydro Dual Speed		N/A	YES	NO	N/A	NO	N/A N/A
	HST Response Control		N/A	YES	YES	N/A	YES	N/A N/A
	Auto Throttle		N/A	YES	ROPS Auto HST Only	N/A	NO	N/A N/A
	Transmission Gear Ranges		Std. DT- 8F/8R GST- 12F/8R	3 Range With Hydro Dual Speed Infinitely Variable	3 Range Infinitely Variable	12F/12R	3 Range Infinitely Variable	16Fx16R Synchro Shuttle Shift 3 Range Infinitely Variable
	Max. traveling speed	mph	16.8	16	18.5	17.3	16.9	15.2 14.1
	Brake		Multi-plate wet disc		Wet disk	Wet Disc		Wet, Multi Disc
PTO clutch		DT/GST- Hyd. Clutch	Master & Hyd. Clutch	Multi-disk, wet	Multi Disc, Wet		N/P	
Tires	Farm	Front	8.3 - 16		7.00-14 6PR	8-16		9.5x16
		Rear	14.9 - 24		11.2-24 6PR	13.6-28		13.6-24
	Turf	Front	29 x 12.5 - 15		27x8.50-15 6PR	27 x 12 -15		29x12.50-15
		Rear	44 x 18 - 20		41x14.00-20	22.5 - 16.1		41x14.00-20
	R4	Front	10 - 16.5		25x8.50-14 6PR R4	10-16.5		10x16.5
		Rear	17.5 - 24		15.00-19.5	17.5-24		43x16.00-20
Hydraulic System	Implement Pump capacity	gpm	9.8		8.6	12		8.2
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	3858		2200	2500		2469
	Front Loader valve & lever		Standard		Standard	Standard		Standard
	Power steering		Standard		Standard	Standard		Standard
Others	Factory Cab Option		N/A	Optional	N/A	N/A		N/A
	Cruise Control		N/A	Standard	N/A	N/P		N/A
Dimensions	Wheelbase	in.	74.6		68	71.5		69
	Tread	Front	51.2		N/P	N/P		N/P
		Rear	DT: 50.6 / GST: 56.5 / HST: 60.2		N/P	N/P		N/P
	Overall Length w/ 3-Point Hitch	in.	129.5		120.2	128.2		121
	Overall Height to top of ROPS	in.	97.4		93.3	97.2		96
	Overall Width (min. tread)	in.	N/P		52.4	65.6		N/P
	Min. ground clearance	in.	14.6		N/P	N/P		N/P
	Min. turning radius w/ brake	ft.	8.9		8.8	9.2		N/P
Weight (w/ ROPS)	lbs.	DT: 3527 / GST: 3571 / HST: 3671		2900	3700		3800	

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.



Grand L4740 Compact Tractors

Grand L 40 Series Competitive Comparison									
MODEL		Kubota L4740		John Deere 4320		New Holland Boomer 50		New Holland Boomer 8N	
		Gear 4WD	HST 4WD	Gear	HST 4WD	Gear 4WD	HST 4WD	CVT	
Engine	Engine gross power	HP	49		48		47		50
	PTO power	HP	41.5	40	40.5	40	39.4	37.1	40
	No. of cylinders		4		4		4		4
	Total displacement	cu.in.	148.5		148.9		153		135.2
	Rated revolution		2700		2400		2600		2800
	Aspiration		Natural	Natural	Turbo	Turbo	Natural		Natural
	Fuel tank capacity	gal.	14.3		13.8		9.5		13
	Double air cleaner		Standard		N/A		Standard		Yes
Drive train	Transmission		GST	HST PLUS	Gear	HST	Gear	HST	CVT
	Stall Guard		N/A	YES	N/A	YES	N/A	N/A	YES
	Hydro Dual Speed		N/A	YES	N/A	NO	N/A	N/A	NO
	HST Response Control		N/A	YES	N/A	YES	N/A	N/A	NO
	Auto Throttle		N/A	YES	N/A	NO	N/A	N/A	YES
	Transmission Gear Ranges		12F/8R	3 Range With Hydro Dual Speed Infinitely Variable	12F/12R	3 Range Infinitely Variable	16Fx16R Synchro Shuttle Shift	3 Range Infinitely Variable	Infinite
	Max. traveling speed	mph	16	16	17.3	16.9	15.2	14.1	18.6
	Brake		Multi-plate wet disc		Multi-disc Wet		Wet, Multi Disc		Wet Disc
PTO clutch		GST- Hyd. Clutch	Master & Hyd. Clutch	Multi-disc Wet		N/P		Wet Disc	
Tires	Farm	Front	8.3 - 16		8 - 16		9.5x16		8 x 16 R1
		Rear	14.9 - 24		13.6 - 28		13.6-24		14.9 x 24 R1
	Turf	Front	29 x 12.5 - 15		27 x 12 - 15		29x12.50-15		27 x 10.5-15 R3
		Rear	44 x 18 - 20		22.5 - 16.1		41x14.00-20		44 x 18-20 R3
	R4	Front	10 - 16.5		10 - 16.5		10x16.5		10 x 16.5 R4
		Rear	17.5 - 24		17.5 - 24		43x16.00-20		17.5L x 24 R5
Hydraulic System	Implement Pump capacity	gpm	9.8		12		8.2		10.5
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2756		2500		2469		2800
	Front Loader valve & lever		Standard		Standard		Standard		Optional
	Power steering		Standard		Standard		Standard		Standard
Others	Factory Cab Option		N/A	Optional	N/P		N/A		Standard
	Cruise Control		N/A	Standard	N/P		N/A		Standard
Dimensions	Wheelbase	in.	74.6		71.5		69		73.5
	Tread	Front	51.2		N/P		N/P		46.4
		Rear	GST: 50.6 / HST: 56.5 / HSTC: 60.2		N/P		N/P		47.5 Min / 67.4 Max
	Overall Length w/ 3-Point Hitch	in.	131.9		128.2		121		122
	Overall Height to top of ROPS	in.	100.6		97.2		96		97.4
	Overall Width (min. tread)	in.	N/P		65.6		N/P		68.3
	Min. ground clearance	in.	14.6		N/P		N/P		12.3
	Min. turning radius w/ brake	ft.	8.9		9.2		N/P		N/P
Weight (w/ ROPS)	lbs.	3671		3700		3800		3760	

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.



Grand L5040 Compact Tractors

Grand L 40 Series Competitive Comparison									
MODEL		Kubota L5040	John Deere 4520		New Holland Boomer 50		New Holland Boomer 8N		
		Gear 4WD	Gear 4wd	HST 4WD	Gear 4WD	HST 4WD	CVT		
Engine	Engine gross power	HP	52	60		47		50	
	PTO power	HP	44	52	50	39.4	37.1	40	
	No. of cylinders		4	4		4		4	
	Total displacement	cu.in.	148.5	148.9		153		135.2	
	Rated revolution		2600	2400		2600		2800	
	Aspiration		Turbo	Turbo	Turbo	Natural		Natural	
	Fuel tank capacity	gal.	14.3	14.5		9.5		13	
	Double air cleaner		Standard	N/A		Standard		Yes	
Drive train	Transmission		GST	Gear	HST	Gear	HST	CVT	
	Stall Guard		YES	N/A	YES	N/A	N/A	YES	
	Hydro Dual Speed		YES	N/A	NO	N/A	N/A	NO	
	HST Response Control		YES	N/A	YES	N/A	N/A	NO	
	Auto Throttle		YES	N/A	YES	N/A	N/A	YES	
	Transmission Gear Ranges		Std. GST- 12F/8R	12F/12R	3 Range Infinitely Variable	16Fx16R Synchro Shuttle Shift	3 Range Infinitely Variable	Infinite	
	Max. traveling speed	mph	15.8	17.3	16.9	15.2	14.1	18.6	
	Brake		Multi-plate wet disc	Wet Disc		Wet, Multi Disc		Wet Disc	
	PTO clutch		Hyd. Clutch	Multi-disc Wet		N/P		Wet Disc	
Tires	Farm	Front	9.5 - 16	8.00 - 16		9.5x16		8 x 16 R1	
		Rear	14.9 - 26	13.6 - 28		13.6-24		14.9 x 24 R1	
	Turf	Front	29 x 12.5 - 15	27 x 12 - 15		29x12.50-15		27 x 10.5-15 R3	
		Rear	44 x 18 - 20	22.5 - 16.1		41x14.00-20		44 x 18-20 R3	
	R4	Front	10 - 16.5	10 - 16.5		10x16.5		10 x 16.5 R4	
		Rear	17.5 - 24	17.5 - 24		43x16.00-20		17.5L x 24 R5	
Hydraulic System	Implement Pump capacity	gpm	9.4	12		8.2		10.5	
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	3858	2500		2469		2800	
	Front Loader valve & lever		Standard	Standard		Standard		Optional	
	Power steering		Standard	Standard		Standard		Standard	
Others	Cruise Control		N/A	N/A	Standard		Standard		
	Toolbox		Standard	Standard				N/P	
Dimensions	Wheelbase	in.	75.4	71.5		69		73.5	
	Tread	Front	in.	52.8	N/P		N/P		46.4
		Rear	in.	52.2	N/P		N/P		47.5 Min / 67.4 Max
	Overall Length w/ 3-Point Hitch	in.	126	128.2		121		122	
	Overall Height to top of ROPS	in.	101	97.2		96		97.4	
	Overall Width (min. tread)	in.	N/P	65.6		N/P		68.3	
	Min. ground clearance	in.	15.7	N/P		N/P		12.3	
	Min. turning radius w/ brake	ft.	9.2	9.2		N/P		N/P	
Weight (w/ ROPS)	lbs.	3803	3700		3800		3760		

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.



Grand L5240 Compact Tractors

Grand L 40 Series Competitive Comparison							
MODEL		Kubota L5240		John Deere 4520		New Holland Boomer 4055 (T2410)	
		HST 4WD		Gear	HST 4WD	Gear	
Engine	Engine gross power	HP	54	60		55	
	PTO power	HP	45	52	50	47	
	No. of cylinders		4	4		4	
	Total displacement	cu.in.	148.5	148.9		135.2	
	Rated revolution		2600	2400		2700	
	Aspiration		Turbo	Turbo	Turbo	Turbo	
	Fuel tank capacity	gal.	14.3	14.5		N/P	
	Double air cleaner		Standard	N/A		N/A	
Drive train	Transmission		HST PLUS	Gear	HST	Gear	
	Stall Guard		YES	N/A	YES	N/A	
	Hydro Dual Speed		YES	N/A	NO	N/A	
	HST Response Control		YES	N/A	YES	N/A	
	Auto Throttle		YES	N/A	YES	N/A	
	Transmission Gear Ranges		3 Range With Hydro Dual Speed Infinitely Variable	12F/12R	3 Range Infinitely Variable	12F/12R	
	Max. traveling speed	mph	13.9	17.3	16.9	N/P	
	Brake		Multi-plate wet disc	Wet Disc		Wet Disc	
PTO clutch		Master & Hyd. Clutch	Multi-disc Wet		Independent		
Tires	Farm	Front	9.5 - 16	8.00 - 16		8 x 16	
		Rear	14.9 - 26	13.6 - 28		14.9 x 24	
	Turf	Front	29 x 12.5 - 15	27 x 12 - 15		27 x 10.5 - 15	
		Rear	44 x 18 - 20	22.5 - 16.1		44 x 18 - 20	
	R4	Front	10 - 16.5	10 - 16.5		12 x 16.5	
		Rear	17.5 - 24	17.5 - 24		18.4 - 24	
Hydraulic System	Implement Pump capacity	gpm	9.7	12		11.6	
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2976	2500		3465	
	Front Loader valve & lever		Standard	Standard		N/P	
	Power steering		Standard	Standard		Standard	
Others	Cruise Control		Standard	N/A	Standard	N/A	
	Toolbox		Standard	Standard		Standard	
Dimensions	Wheelbase	in.	75.4	71.5		N/P	
	Tread	Front	in.	52.8	N/P		56.4
		Rear	in.	52.2	N/P		52.8
	Overall Length w/ 3-Point Hitch	in.	135	128.2		N/P	
	Overall Height to top of ROPS	in.	101	97.2		N/P	
	Overall Width (min. tread)	in.	N/P	65.6		N/P	
	Min. ground clearance	in.	15.7	N/P		N/P	
	Min. turning radius w/ brake	ft.	9.2	9.2		N/P	
Weight (w/ ROPS)	lbs.	3902	3700		3377		

N/A = Not Available

N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.



Grand L5740 Compact Tractors

Grand L 40 Series Competitive Comparison						
MODEL		Kubota L5740	John Deere 4720	New Holland Boomer 4060		
		HST 4WD	HST 4WD	Gear		
Engine	Engine gross power	HP	59	66	60	
	PTO power	HP	50	56	51	50
	No. of cylinders		4	4	4	
	Total displacement	cu.in.	148.5	148.9	135.2	
	Rated revolution		2700	2400	2800	
	Aspiration		Turbo	Turbo	Turbo	
	Fuel tank capacity	gal.	14.3	14.5	13.5	
	Double air cleaner		Standard	N/A	N/A	
Drive train	Transmission		HST PLUS	HST	Synchro Shuttle	Electrohydraulic Shuttle
	Stall Guard		YES	YES	N/A	N/A
	Hydro Dual Speed		YES	NO	N/A	N/A
	HST Response Control		YES	YES	N/A	N/A
	Auto Throttle		YES	YES	N/A	N/A
	Transmission Gear Ranges		3 Range With Hydro Dual Speed Infinitely Variable	3 Range Infinitely Variable	12F/12R	12F/12R
	Max. traveling speed	mph	16.1	16.9	N/P	N/P
	Brake		Multi-plate wet disk	Wet Disk	Wet Disk	
PTO clutch		Master & Hyd. Clutch	Independent	Independent		
Tires	Farm	Front	9.5 - 16	8.00 - 16	8 x 16	
		Rear	14.9 - 26	13.6 - 28	14.9 x 24	
	Turf	Front	29 x 12.5 - 15	27 x 12 - 15	27 x 10.5 - 15	
		Rear	44 x 18 - 20	22.5 - 16.1	44 x 18 - 20	
	R4	Front	10 - 16.5	10 - 16.5	12 x 16.5	
		Rear	17.5 - 24	17.5 - 24	18.4 - 24	
Hydraulic System	Implement Pump capacity	gpm	9.8	12	12	
	3-Point Hitch lift capacity @ 24" behind lift point	lbs.	2976	2500	3465	
	Front Loader valve & lever		Standard	Standard	N/P	
	Power steering		Standard	Standard	Standard	
Others	Cruise Control		Standard	Standard	N/A	
	Toolbox		Standard	Standard	Standard	
Dimensions	Wheelbase	in.	75.4	71.5	N/P	
	Tread	Front	in.	52.8	N/P	56.4
		Rear	in.	52.2	N/P	52.8
	Overall Length w/ 3-Point Hitch	in.	135	128.2	N/P	
	Overall Height to top of ROPS	in.	101	97.2	N/P	
	Overall Width (min. tread)	in.	N/P	65.6	N/P	
	Min. ground clearance	in.	15.7	N/P	N/P	
	Min. turning radius w/ brake	ft.	9.2	9.2	N/P	
Weight (w/ ROPS)	lbs.	3902	4345	3377		

N/A = Not Available N/P = Not Published

This comparison of specifications is based upon the most reliable information obtained by Kubota at the time of publication. It is correct to the best of our knowledge. Kubota reserves the right to change the specifications relating to its products without notice.