

Stainless Steel Belt Conveyor - 7-3/4 in. wide

Mfg:

Model:

Stock No.: NOI8029

Serial No.:

Stainless Steel Belt Conveyor. Belt width: 7-3/4 in. Maximum aperture/clearance above belt: 8-1/4 in. W x 10-1/2 in. H. Duty Master Electric Motor, 3/4 hp, 1725 rpm, 208-230/460 V, 2.2/1.1 amps, 60 Hz, 3 phase. Tigear Speed Reducer. Conveyor infeed/exit height: 7-1/4 in. Overall dimensions: 12 ft. L x 5-1/2 in. L x 1 ft. 4 in. W x 2 ft. 2-3/4 in. H.



