

Vibratory Bowl Cap Feeder

Mfg:

Model:

Stock No.: NOI8045

Serial No.:

Vibratory Bowl Cap Feeder. Maximum product width: 1-1/2 in. (38 mm). Power requirements: 120 V, 60 Hz, 1 phase. Cap-chute end position is 41 in. high from ground. Unit has an actuator height adjuster. Bowl dimensions: 1 ft. 5-1/4 in. dia. x 4-5/8 in. H. Open top funnel hopper dimensions: 2 ft. 2 in. L x 2 ft. 2 in. W x 1 ft. 3 in. H. Outlet: 11-1/2 in. L x 8-1/8 in. W x 3 in. H (chute to feed bowl). Overall dimensions: 4 ft. 4 in. L x 2 ft. 3 in. W x 6 ft. 10 in. H.









