

Goulds Centrifugal Pump

Mfg: Goulds

Model:

Stock No. OIP038.

Serial No.

Goulds Centrifugal Pump. Size: 3x4. 316 stainless steel. Impeller diameter: 7 in. Double mechanical seals with water flush. General Electric Motor: 7.5 hp, 1760 rpm, 575 V, 8.7 amps, 60 cycles, 3 phase. Overall dimensions: 46 in. L x 16 in. W x 23-1/2 in. H.

