

Fristam Sanitary Centrifugal Pump

Mfg: Fristam

Model: FP1741/205F

Stock No. NOIP8008.

Serial No. 141169035

Fristam Sanitary Centrifugal Pump. Model: FP1741/205 F. S/N: 141169035. Capacity: 175 gpm. Material of construction: 316 stainless steel. Impeller diameter: 8 in. Baldor Industrial Motor, 7-1/2 hp, 1725 rpm, 208-230/460 V, 21.5-20/10 amps, 60 Hz, 3 phase. Inlet: (1) 2-1/2 in. dia. S-line fittings. Outlet: (1) 2 in. dia. S-line fittings. Overall dimensions: 2 ft. 1 in. L x 10 in. W x 13 in. H.



