

## 1995 Fristam Sanitary Centrifugal Pump

Mfg: Fristam

Model: FP 722145

Stock No.: NPPC204

Serial No.: 22175196

1995 Fristam Sanitary Centrifugal Pump. Model: FP 722145. S/N: 22175196. Flow rate for new pump is 90 gpm with required horsepower and pressure at 55 psi. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Material of construction: 316L stainless steel construction. Impeller diameter: 5-1/2 in. (145 mm.) Seal Option: Double mechanical seals with flush. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 13.2-12/6 amps, 60 Hz, 3 phase. These heavy-duty, high performance sanitary centrifugal pumps handle demanding applications such as viscous, hot, or abrasive products and can be used for vacuum withdrawal from evaporators. Inlets: (1) 2 in. dia. S-line fittings. Outlet: (1) 1-1/2 in. dia. S-line fittings. Overall dimensions: 2 ft. 4 in. L x 1 ft. 1 in. W x 1 ft. 5 1/2 in. H. (ACN32).

