

## Stainless Steel Tank with Lightning Mixer-320 Gallon

Mfg:

Model:

Stock No. OI187.

Serial No.

Stainless Steel Tank with Lightning Mixer-320 Gallon. Lightning Mixer: 1 hp, 1730 rpm, 208-220/440V, 3.2/1.6 amps, 60 Hz, 3 phase. (2) Propellers: small propeller (3) 2-3/4 in. blades, large propeller (3) 5-3/4 in. blades (2) 4 in. W x 12 in. L rectangular sight/measuring glasses. Inlets: (1) 19 in. Dia. Manway. (1) 2-1/2 in. Andrews type D coupling w/ open/close valve. (1) 2-1/2 in. threaded female (covered). Outlets: 2 in. threaded female outlet port w/ open/close valve. Model: n/a, S/N n/a. Overall Dimensions: 55 in. L x 42.5 in. W x 100 in. H.



