

Stainless Steel Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No. OI272.

Serial No.:

Stainless Steel Shell and Tube Heat Exchanger. (108) 2 in. dia. x 10 ft. L stainless steel multi-tubes. Heat transfer surface area: approx. 565 sq. ft. Volume: 175 gallon. Inlets: (1) 1-1/2 in. dia. S-line fitting (sprayball), (1) 12 in. dia. flanged port (media), (1) 20 in. dia. flange port (product). Outlets: (1) 2 in. dia. FNPT (media), (1) 2-1/2 in. dia. FNPT (media), (1) 8 in. dia. flanged port (product). Overall dimensions: 4 ft. 8 in. L x 4 ft. W x 15 ft. H.



