

Stainless Steel Two Barrel Scrape Surface Heat Exchanger

Mfg:

Model:

Stock No. RAAF142.93a

Serial No.:

Stainless Steel Two Barrel Scrape Surface Heat Exchanger. (2) 15 in. dia. x 10 ft. 10 L barrels with (42) 1 in. L x 3 in. W bakelite scrapers. Setup for chilling with freon. (2) Erole Marelli Motors, 30 hp, 1507 rpm, 265/460 V 9.5/5.5 amps, ratio 10.4, final rpm: 163. Inlets: (2) 1-1/2 in. dia. NPT (male), (1) 2 in. dia. media port. Outlets: (2) 1-1/2 in. dia. NPT (male). Overall dimensions: 13 ft. 7 in. L x 24 in. W x 66 in. H





