

Armstrong Vertical In-Line Centrifugal Pump

Mfg: Armstrong

Model: 4300

Stock No. OIP076.

Serial No. 406278

Armstrong Vertical In-Line Centrifugal Pump. Model: 4300. S/N: 406278. Size: 6x6x10. Capacity: 100 gpm @ 47 tdh. Baldor Industrial Motor: 25 hp, 1760 rpm, 230/460 V, 62/31 amps, 60 Hz, 3 phase. Vertical In-Line pumps, being integral components of the pipework, eliminate need for inertia bases, springs, flexible pipe connectors, field grouting and alignment. Pipe hangers are the only supports required. Fully enclosed bronze impeller. Split-coupled design allows mechanical seal replacement without costly removal of the motor or pump from the piping. Inlets: (1) 6 in. inlet port. Outlets: (1) 6 in. outlet port. Overall dimensions: 56 in. L x 20 in. W x 65 in. H.

