

1996 Safeline Metal Detector

Mfg: Safeline

Model: STD20X08/SS/100/HD

Stock No: RBFM257.100

Serial No: 21692

1996 Safeline Metal Detector. Model: STD20X08/SS/100/HD. S/N: 21692. Reference No. 10987-01. M/C: 013. Module Hardware Version: 82. Firmware Version: 1.251. Maximum aperture/clearance: 1 ft. 7-1/4 in. W x 6-5/8 in. H. Infeed/exit height: 3 ft. 2 in. Sensitivity: 2.5 mm Fe, 3.5 mm non-Fe, 5 mm stainless steel. Features automatic balancing and selectable high and low product speeds. Conveyor dimensions: 7 ft. 1 in. L x 19 in. W, with automatic reject system and (2) 1 ft. 11-1/2 in. L x 1 ft. 11-1/2 in. W x 5-3/4 in. H reject bins. Baldor motor, 1/2 hp, 1725 rpm, 230/460 V, 1.6/0.8 amps, 60 Hz, 3 phase. Tigear gear reducer, ratio: 40. Final rpm: 43. Power supply: 120 V, 0.5 amps, 60 Hz, single phase. Overall dimensions: 7 ft. 3 in. L x 6 ft. W x 4 ft. 5 in. H.(ACN180).











