

Fristam FPX-Series Sanitary Centrifugal Pump

Mfg: Fristam

Model: FPX 3532

Stock No: OIP140

Serial No: 353268129

Fristam FPX-Series Sanitary Centrifugal Pump. Model: FPX 3532. S/N: 353268129. Capacity: 180 gpm @ 90 tdh (39 psi using specific gravity of water = 1). Displacement per Revolution: 0.057. 316 Stainless Steel Interior Components. Seal Option: single mechanical, chrome oxide/carbon. Impeller diameter: 5 in. (130 mm). Baldor Industrial Motor, 7 ½ hp, 3450 rpm, 208-230/460 V, 18.5-17.4/8.7 amps, 60 Hz, 3 phase. The FPX-series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX-series is well known for quiet, efficient, low maintenance operations. Typical applications: bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical separation, reverse osmosis, in-line mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, fermentation. Inlet: (1) 2 ½ in. dia. S-line fitting. Outlet: (1) 2 in. dia. S-line fitting. Overall dimensions: 2 ft. 3-1/4 in. L x 1 ft. 1 in. W x 1 ft. 2-1/2 in. H. (ACN30).





