

1996 Kinney Liquid Ring Vacuum Pump

Mfg: Kinney

Model: KLRC-75 KFA

Stock No: RBFM750MB

Serial No: 96-1938 07153-1

1996 Kinney Liquid Ring Vacuum Pump. Model: KLRC-75 KFA. S/N: 96-1938 07153-1. Flow rate for new pump is 70 cfm and pressure as low as 4 Torr (dependent of vapor pressure of sealing liquid). Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (1) Vacuum gauge. Oil separator tank dimensions: 9-3/4 in. dia. x 1 ft. 10 in. H. U.S. Electrical motor: 5 hp, 1740 rpm, 208-230/460 V, 17.2/8.6 A, 60 Hz, 3 phase. Inlets/Outlets: (2) 2 in. FNPT. (2) 1-1/2 in FNPT. (1) 1/2 in. FNPT. (1) 5/8 in. port. Overall dimensions: 3 ft. 5 in. L. x 2 ft. 6-1/4 in. W. x 2 ft. 10-1/2 in. H.





