

## G&H Centrifugal Pump

Mfg: G&H

Model: GHC-1/162

Stock No. PPCC004.

Serial No. 88-2-1/710

G&H Centrifugal Pump. Model: GHC-1/162. S/N: 88-2-1/710. Capacity: 170 gpm @ 21 tdh. Impeller diameter: 5-3/4 in. Single mechanical seal. Motor, 3 hp, 1730 rpm, 200-230/480 V, 9.7-9.8/4.9 amps, 60 Hz, 3 phase. Previously used by Lifesavers candy in Holmo, MI. Besides being completely CIP-able, these pumps provide gentle handling of products, require less power to operate, and provide easy maintenance at low costs. Inlets: (1) 2-1/2 in. dia. S-line fitting. Outlets: (1) 2 in. dia. S-line fitting. Overall dimensions: 22 in. L x 14 in. W x 13 in. H.

