

Dual APV Stainless Steel Feeding Hopper Tank and Pumps

Mfg: Crepaco

Model: R4RI

Stock No: RBFM824.20

Serial No: H-9785-95, P822 2-0298

Dual APV Stainless Steel Feeding Hopper Tank and Pumps. Capacity: 360 gallons dry capacity. (2) Pump Model: R4RI S/N: P822 2-0298, S/N: H-9785-95 and P822 2-0298 Inlets: 6 ft. L. x 3 ft. W. x 1 ft. 6 in. H. (infeed hopper) Outlets: (2) 3-1/2 in. dia. NPT fittings. Inside-straight wall dimensions: 6 ft. L. x 2 ft. 11 in. W. x 3 ft. 8 in. H. Overall dimensions: 6 ft. 5 in. L x 3 ft. 5 in. W x 4 ft. 10 in. H.





