

2002 Square D ISO-FLEX® Medium Voltage Controller

Mfg: Square D

Model: 4

Stock No: RBFM845a

Serial No:

2002 Square D ISO-FLEX® Medium Voltage Controller. Model: 4. Class E2, Factory order number: 17-15018462-005. Catalog number: RG44D Nominal system voltage: 4000 / 4160 V, rated maximum voltage 5 kV, continuous current 360 amp, central voltage 120 VAC volts. Impulse withstand: 60 kV, Horizontal bus rating: 1200A. Power fuse size: 9R. Control voltage: 120 VAC. Features include: front and rear access, and a NEMA 1 indoor, painted and gasketed enclosure. This unit is equipped with a General Electric 469 Motor Management Relay® motor protection system. Features include: comprehensive motor protection plus voltage dependant overload curves, torque metering and protection, broken rotor bar protection; complete asset monitoring for temperature, analog I/O, demand and energy. Previously installed at Bryan Foods in 2002 and removed from service in April 2007. Last used with a 1167 hp compressor. Run hours: 23919. Overall dimensions: 3 ft. 1 in. L x 2 ft. 11 in. W x 8 ft. 4 in. H and 2 ft. 11-1/2 in. L x 2 ft. 6-1/2 in. W x 8 ft. 4 in. H.





