

FES 575 HC / Mycom 250L Rotary Screw Compressor Package

Mfg: FES Mycom

Model: 575HE / 250L

Stock No: RCJF1521.15

Serial No: 2512-773

FES 575 HC / Mycom 250L Rotary Screw Compressor Package. Model: 575-HE / 250L. S/N: 2512-773. Refrigerant: last used with R-717 (ammonia). Displacement: 1,670 cfm. Control panel: model: 385V, S/N: 87-0259-0301-02. Leak test pressure: 313. Hydrostatic test pressure: 470. Oil Separator: S/N: 87008. Nat'l Bd: 3182. MAWP: 250 PSI at 200°F. MDMT: 200°F. Radius: elliptical ends. Pump: Viking pump. Motor: 7.5 hp, 1175 rpm, 230/460 V, 20.4/10.2 amps, 60 Hz, 3 phase. Inlets/Outlets: (1) 5 in. dia. port. (1) 4 in. dia. port. (2) 1 ¼ in. dia. port. (1) 1 in. dia. port. Overall dimensions: 13 ft. L x 4 ft. 5 in. W x 9 ft. 6 in. H. Compressor runtime: 40074 hrs.(ACN950-87).





