

Walker Stainless Steel Jacketed Blend Tank - 5000 Gallons

Mfg: Walker

Model: EQ 25-000

Stock No: RCJF1455.30

Serial No: 896-4679

Walker Stainless Steel Jacketed Blend Tank. Model: E Q 25-000. S/N: 896-4679. Approximate capacity: 5000 gallons. Inside dimensions: straight wall: 8 ft. 10 in. dia. x 11 ft. 11 in. H. Kawasaki "Staffa Transmissions" agitator motor, model no.B200/S, serial no.138892, outside shaft dia:3-1/2 in., inside shaft dia: 4-1/2 in. Designed for continuous output, this motor is rated for 174 HP and 175 rpm. (1) manhole: 19 in. (2) 4 in. spray balls. (5) 94 in. L x 9 in. H propellers. (2) 3 in. ACME inlets. (1) 3 in. S-Line inlet. (1) 5 in. top vent hole. (1) 2 in. S-Line outlet. (3) Outlet flanges: 3 in. flange dia. with (4) mounting holes: 3/4 in. dia., adjacent distance: 4-1/4, opposite distance: 6 in. Outlet flange dia. 6-3/8 in., with (8) mounting holes: 7/8 in. dia. adjacent distance: 3-3/4 in., opposite distance: 9-5/8 in. Outlet flange dia.2-7/8 in., with (4) mounting holes: 3/4 in. dia. adjacent distance: 3-3/8 in. opposite distance: 4-3/4 in. Originally installed with Cargill Juice and used in a 25°Bx orange juice application using fully flooded ammonia to cool product. Overall dimensions: 9 ft. 2 in. dia. x 17-1/2 ft. H.











