

Stainless Steel Filter Screens

Mfg:

Model:

Stock No: RCJF1756.1

Serial No:

(6) Stainless Steel Filter Screens. Designed for inline filtration of large particles in varieties of processes.

Filter 1: Inner screen mesh opening diameter: 0.030 in. Outer screen mesh opening diameter: 0.25 in. Overall dimensions: 11 ½ in. L x 11 ½ in. W x 20 in. H.

Filter 2: Screen mesh opening diameter: 0.125 in. Filter ID: 5 ½ in. Filter OD: 7 in. Filter length: 12 in. Overall dimensions: 7 in. L x 7 ½ in. W x 17 ½ in. H.

Filter 3: Inner screen mesh opening diameter: 0.035 in. Outer screen mesh opening diameter: 0.25 in. Filter opening: OD: 21 ½ in. ID: 21 in. Filter closed end: OD: 9 ¾ in. Overall dimensions: 21 ½ in. L x 21 ½ in. W x 31 ½ in. H.

Filter 4: Inner screen mesh opening diameter: 0.035 in. Outer screen mesh opening diameter: 0.25 in. Filter opening: OD: 21 ½ in. ID: 21 in. Filter closed end: OD: 9 ¾ in. Overall dimensions: 21 ½ in. L x 21 ½ in. W x 31 ¼ in. H.

Filter 5: Inner screen mesh opening diameter: 0.025 in. Outer screen mesh opening diameter: 0.25 in. Filter opening: OD: 10 ½ in. ID: 9 ½ in. Filter closed end: OD: 6 in. Filter height: 16 in. Overall dimensions: 10 ½ in. L x 10 ½ in. W x 16 in. H.

Filter 6: Inner screen mesh opening diameter: 0.030 in. Outer screen mesh opening diameter: 0.25 in. Filter opening: OD: 10 ½ in. ID: 9 ½ in. Filter closed end: OD: 6 in. Filter height: 16 in. Filter holder inlet/outlet flanges: OD: 9 in. ID: 4 in. Ports: (Qty 2) ¼ in. FNPT for pressure gauges. Overall dimensions: 15 in. L x 20 in. W x 27 in. H.













