

Garvey Bi Flo Accumulation Table

Mfg: Garvey

Model: 9700

Stock No. RCPK279.23

Serial No. 14720

Garvey Bi Flo Accumulation Conveyor. Model: 9700. S/N: 14720. 304 stainless steel. #4 Finish. Features include low-friction thermoplastic belts and formed stainless steel with plastic facing guide rails. Maximum aperture/clearance above belt: 2-1/2 in. Adjustable clearance to a maximum height of 3 in. Infeed and discharge can be accomplished by end to end transfer or preferably side transfer due to Garvey's exclusive flush side transfer sections where no dead plates are required. Height at conveyor infeed/exit: 34 in. Multiple Lane Infeed/Single Lane Outfeed. (6) Winding sections. Width of conveyor sections: #1- 1 ft. 6 in., #2- 1 ft., #3- 7-1/2 in., #4- 7-1/2 in., #5- 1 ft., #6- 1 ft. 6 in. Sections 2 and 5 extend 3 ft. from the back end while sections 3 and 4 extend 3 ft. forward. (2) Baldor Industrial Motors, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. (2) SM-Cyclo Motor Drives, 15 ratio, 115 rpm (final). Overall dimensions: 26 ft. L x 6 ft 6 in. W x 40 in. H.



