

## Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX1151-270

Stock No. RLOL717.8

Serial No. FPX115174040

Fristam FPX-Series Centrifugal Pump. Model: FPX1151-270. S/N: FPX115174040. Capacity: 720 gpm @ 30 psi and 70 head/ft. Impeller diameter: 9-1/2 in. (240 mm). Baldor Industrial Motor, 25 hp, 1760 rpm, 230/460 V, 64/32 amps, 60 Hz, 3 phase. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations. Inlets/outlets: (2) 4 in. S-line fittings. Overall dimensions: 35 in. L x 18 in. W x 17 in. H.



