

Creamery Package Rota-Pro Swept Surface Heat Exchanger

Mfg: Creamery Package

Model:

Stock No. RCPK544.8a

Serial No. HP-2-125-S

Creamery Package Rota-Pro Swept Surface Heat Exchanger. S/N: HP-2-125-S. Heating surface area: 9.5 ft. sq/cylinder. Glycol-cooled. Standard ASME cylinder jackets are provided for heating with water or steam media up to 450 °F or cooling with water, brine, glycol or other suitable liquid media. Inner cylinder dimensions: 6 in. dia x 48 in. L. Chrome plated nickle barrel. Rotating dashers, with fixed scraper blades, continuously sweep the cylinder surface clean of product, simultaneously producing a highly desirable level of product mixing and agitation contributing to consistency in final product identity. Louis Allis Motor, 15 hp, 1770 rpm, 440 V, 20 amps, 60 Hz, 3 phase. Inlets: (2) 2-1/2 in. dia. threaded fittings, (1) 1-1/2 in. dia. bevel with hex nut (media). Outlets: (2) 2 in. dia. threaded fittings, (1) 1-1/2 in. dia. media port. Overall dimensions: 88 in. L x 51 in. W x 65 in. H.



