

Atlas Shell and Tube Heat Exchanger – 79.5 sq. ft.

Mfg: Atlas

Model:

Stock No.: RPAG689

Serial No.: 4650

Atlas Shell and Tube Heat Exchanger – 79.5 sq. ft. S/N: 4650. Nat'l Bd: 3416. Tube material: 316 stainless steel. Number of tubes: 76. Tube dimensions: 1/2 in. dia. x 8 ft. L. Heat transfer surface area: approx. 79.5 sq. ft. Tube volume: 6 gal. Shell side MAWP: 150 psi @ 350°F. Tube side MAWP: 150 psi @ 350°F. Inlet: (1) 3 in. dia. flanged port. Outlet: (1) 3 in. dia. flanged port. Product flange diameter: 15 in. Center to center measurement between flange bolt holes: 3-1/2 in. Overall dimensions: 8 ft. L x 1 ft. 8 in. W x 2 ft. 1-1/2 in. H.

