

## Waukesha 130 Positive Displacement Pump

**Mfg: Waukesha Cherry-Burrell**

**Model: 130**

**Stock No.: RCSC379.47a**

**Serial No.: 385490 05**

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 130. S/N: 385490 05. 3A Sanitary. Flow rate for new pump is 150 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.254 gallon. Estimated flow rate with this gear drive is 49 GPM. SEW-Eurodrive gear drive ratio: 9.06 (final RPM 139). Baldor Super-E Motor: 5 HP, 460V, 6.6 amps, 1750 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 3 in. dia I-line fittings. Overall dimensions: 4 ft. 3 in. L x 1 ft. 5 in. W x 1 ft. 7 in. H. (ACN125-185)







