

Filler Parts Stainless Steel

Mfg:	Model:
Stock No. SABE043.1a	Serial No.

Filler Parts. Stainless steel. Maximum aperture/clearance above belt: 8 in. W x 1/2 in. H. Height at conveyor inlet/outlet: 38 in. Dual roller chains move (20) 6 in. L x 5-1/2 in. W dies, each with a square cut-out. Dies travel under a 4-1/2 in. dia. x 7-1/2 in. L press roller and a 1-1/2 in. dia. x 7-1/2 in. long roller with horizontal cutting blade. Veeder Root 5-digit counter. Dayton SCR variable speed control box: 1/35-1/6 hp. Ogden ETR-9090 digital temperature sensor: 120 V, 15 amps. Dayton DC Gearmotor, 1/8 hp, 54 rpm (final), 34:1 ratio, 130 in-lb. torque. Overall dimensions: 72 in. L x 24 in. W x 62 in. H. Dayton SCR Control Box, Model: 6X165C, 1/35-1/6 hp, 115 V, 60/50 Hz, 1 phase.



