

Autoprod Cup Filler Tray Dropper

Mfg: Autoprod

Model: FP

Stock No. SABE145.5

Serial No. AP-789

Autoprod Cup Filler Tray Dropper. Model: FP. S/N: AP-789. Previously used for filling and sealing table syrup cups. Tray dimensions: 1 ft. L x 7-1/4 in. W. Number of slots per tray: 25. Slot dimensions (for cups): 1-5/8 in. L x 1-1/8 in. W. Infeed hopper dimensions: 2 ft. 4 in. L x 1 ft. 5 in. W. Number of filling valves: 25. Valve diameter: 1/8 in. Cup Dispenser, dimensions: 1 ft. L x 7-1/4 in. W. Glue Roller Applicator, dimensions: 2-1/2 in. dia. x 11 in. L. Plate Press, dimensions: 1 ft. L x 7-1/4 in. W. Glue Drying Plate, dimensions: 1 ft. x 7-1/4 in. W. Razor Blade Cup Individualizer. Vacuum Tube Dispenser, number of vacuum tubes: 25. Continental Hydraulics Inc. Hydraulic Pump, Model: PVR1-12010-RM-0-38-F, capacity: 12 gpm, input speed: 3800 rpm. Magnatek Electric Motor, 5 hp, 1740 rpm, 230/460 V, 13.6/6.8 amps, 60 Hz, 3 phase. Hydraulic Oil Reservoir Tank- 30 Gallon, inside straight-wall dimensions: 2 ft. 4 in. L x 1 ft. 6-1/4 in. W x 1 ft. 2 in. H. Baldor Electric Motor, 3/4 hp, 1725 rpm, 575 V, 1.2 amps, 60 Hz, 3 phase. Worm Gear Speed Reducer with motor, ratio: 30, input rpm: 1750. Electronic Machine Parts Gear Reducer, Model: 11. Conveyor infeed/exit height: 2 ft. 8 in. Inlets: (1) 2 ft. 4 in. L x 1 ft. 5 in. W product infeed. Overall dimensions: 11 ft. 11 in. L x 4 ft. 7-1/2 in. W x 6 ft. 3 in. H. (XMR14a)







