

Flex Conveyor with Dual Chain Drive

Mfg:

Model:

Stock No. SABE001.

Serial No.:

Flex Conveyor with Dual Chain Drive. Baldor Motor, 1.7 hp, 2 rpm, 208-230/460 V, 1.3-1.21-0.6 amps, 60 Hz, 3 phase. Boston Motor Drive, 50 ratio, 109 lb-in. Block Plate: 13 in. W x 12 in. H. Maximum aperture/clearance: 4 in. W x 1-1/2 in. H. (4) Joyce Dayton. 6 ft. L conveyor. Joyce/Dayton Corp height adjustment crank, Model: WJ500-12, S/N: J95-11928, 500 lbs cap. Banner Mini Beam. Overall dimensions: 73 in. L x 34 in. W x 60 in. H.



