

Stainless Steel Cutters


Mfg:

Model:



Stock No. SACH102.2



Serial No.

Stainless Steel Cutter. Dimensions: 38 in. x 34-1/2 in. and the shaft: 19 in. H. 25 divisions each one with 19 cables in vertical and horizontal, 3/8 of clearance, missing 11 cables. Overall dimension: 44 in. L x 35 in. W x 19 in. H.





Stainless Steel Cutter. Dimensions: 29-1/2 in. x 26 in. and the shaft: 14 in. H. 4 divisions each one with 18 cables in vertical, 3/8 of clearance, missing 10 cables. Overall dimension: 29-1/2 in. L x 26 in. W x 14 in. H.








Stainless Steel Cutter. Dimensions: 29-1/2 in. x 26 in. and the shaft: N/A. 4 divisions each one with 15 cables, 3/8 of clearance, missing 8 cables. Overall dimension: 29-1/2 in. L x 26 in. W x 3 in. H.



Stainless Steel Cutter. Dimensions: 35 in. x 32 in. and shaft: 17 in. H. 10 divisions each one with 17 cables in horizontal, 3/8 of clearance, missing 10 cables. Overall dimension: 35 in. L x 32 in. W x 17 in. H.



Stainless Steel Cutter. Dimensions: 32 in. x 34 in. and the shaft: (2) 18 in. H. 10 divisions each one with 17 cables in vertical, 3/8 of clearance, missing 15 cables. Overall dimension: 34 in. L x 32 in. W x 18 in. H.



Stainless Steel Cutter. Dimensions: 39 in. x 32 in. and the shaft: 48 in. H x 13 in. W. 8 divisions each one with 19 cables in vertical, 3/8 of clearance, missing 27 cables. Overall dimension: 39 in. L x 32 in. W x 48 in. H.

