

PDC Cap Sealer

Mfg: PDC

Model: 75C-ER

Stock No. SAF302a.2a

Serial No. 110

PDC Cap Sealer. Model: 75C-ER. S/N: 110. Power supply: 240 V, 12 amps, single phase, total hp: 1.5. (2) 2 ft. 1 in. dia. film rolls. Maximum aperture/clearance: 3-1/2 in. W x 11 in. H. Timing screw dimensions: 4 ft. dia. x 3 ft. L. Maximum bottle size: 3-1/2 in. R-E Rate Meter. PDC Control Panel. Magnatek Motor, 1 hp, 1735 rpm, 180 V, 5.35 amps. Dodge Tigear Right Angle Drive. Emerson Electric Co. Speed Reducer. Baldor Electric Motor with Feed Drive, 1/4 hp, 180 DCV, 1.3 amps, reduced output, 68 rpm, ratio: 45, torque: 135 in. lbs. Film Clutch Brake. Baldor Gear Motor, 1/4 hp, 125 rpm, 180 DCV, 1.2 amps, ratio: 20, torque: 100 in. lbs. Conveyor infeed/exit height: 3 ft. Overall dimensions: 10 ft. 7 in. L x 3 ft. 6 in. W x 7 ft. 2 in. H.















