

Bran+Luebbe Auto In-line Blend System / 3 Metering Pumps

Mfg: Bran+Luebbe

Model: N-C33

Stock No: SCJC178.5a

Serial No: A9522

Bran+Luebbe Auto In-line Blend System / 3 Metering Pumps. Type: N-C33. Machine Number: A9522. Approximate capacities: "A" pump: 17 gpm, "C" pump: 17 gpm, and "D" pump: 23 gpm. Product contact surfaces: 316 stainless steel. Working pressure: 100 psi. Baldor Industrial motor: 15 hp, 1760 rpm, 230/460v, 38/19 a, 60 Hz, 3 phase. Inlets/outlets: (3) 2 in. S-line, (3) 2 in. ports, (2) 2-1/2 in. ports. Metering pumps address products that need to be blended and metered to include light to heavily viscous foods products. This unit was previously in service pumping varieties of sugar and corn syrups. Overall dimensions: 6 ft. L x 2 ft. 8 in. W x 6 ft. 3 in. H.





