

Atlas Copco Air Screw Compressor

Mfg: Atlas Copco

Model:

Stock No. SDYC002.

Serial No. ARP878

Atlas Copco Air Screw Compressor. Type: GAU709. S/N: ARP878 212. System Nat'l Bd: 21494. Compressor MAWP: 126.18 psi (8.7 bar). Compressor run time: 44409 hrs. Part No: 1202 3787-02, shell thickness: 0.315 in., head thickness: 0.315 in. Oil Separator with level indicator, MAWP: 160 psi at 248 °F, shell thickness: 0.197 in, head thickness: 0.197 in. Condenser dimensions: 28 in. L x 4-1/2 in. W x 44 in. H. Digital control panel with touchpad controls, Type: 1900.0150.03, electrical requirements: 115 V, 60 Hz, 1 phase. General Electric Motor, 75 hp, 3565 rpm, 230/460 V, 177.8/88.9 amps, 3 phase. Key aspects of unit are: unload/normal, reset-start, and stop switches, voltage on, automatic operator, oil separator, oil filter, air filter. Outlets: (1) 1-1/2 in. dia. NPT (male). Overall dimensions: 98 in. L x 45 in. W x 75 in. H.



