

## **Bran+Luebbe Auto In-line Blend System with 4 Metering Pumps**

**Mfg: Bran+Luebbe**

**Model: N-C34-K31**

**Stock No: SCJC179.5a**

**Serial No: A1501**

Bran+Luebbe Auto In-line Blend System with 4 Metering Pumps. Machine No: A1501. Type: N-C34-K31. Approximate capacities: "A" pump: 24 gpm, "B" pump: 6 gpm, "C" pump: 4 gpm, and "D" pump: 3 gpm. Product contact surfaces: 316 stainless steel. Working pressure: 90 psi. Baldor Industrial motor: 5 hp, 870 rpm, 230/460 v, 18.8/9.4 a, 60 Hz, 3 phase. Metering pumps address products that need to be blended and metered to include light to heavily viscous food products. This unit was previously in service pumping varieties of syrups and fruit concentrates. Inlets/outlets: (4) 2 in. outer dia. and 7/8 in. inner dia., (2) 2 in. S-line, (2) 1-1/2 in. S-line. Overall dimensions: 4 ft. 8 in. L x 2 ft. 7 in. W x 5 ft. 2 in. H.







