

1997 Cornell Refrigeration Centrifugal Pump

Mfg: Cornell

Model: 3CB-10-6

Stock No.: SELM160.4a

Serial No.: 10192

1997 Cornell Refrigeration Centrifugal Pump. Model: 3CB-10-6. S/N: 10192. Flow rate for new pump is 400 gpm with required horsepower and pressure. Discuss with salesperson your process to determine if this refurbished pump should handle your specific duty. Impeller size: 15.22 in. Seal option: John Crane, 1.62 in., T-2, double mechanical seal with pressurized barrier fluid lubrication system. Constructed of ASTM A536 60-40-18 ductile iron. Baldor industrial motor 10 hp, 1170 rpm, 230/460 V, 28/14 amps, 60 Hz, 3 phase. Inlets: (1) 6 in. dia. suction flanged port. Outlets: (1) 3 in. dia. discharge flanged port. Overall dimensions: 2 ft. 4 in. L x 2 ft. 1 in. W x 2 ft. 2 in. H. (ACN104)



