

## Cornell Centrifugal Refrigeration Pump

Mfg: Cornell

Model: 3CB-F6K

Stock No.: SELM158.2

Serial No.: 68008

Cornell Refrigeration Centrifugal Pump. Model: 3CB-F6K. S/N: 68008. BM: E068A-A01. Flow rate for new pump is 400 gpm with required horsepower and pressure. Discuss with salesperson your process to determine if this refurbished pump should handle your specific duty. Impeller size: 15.22 in. Shaft diameter: 1-3/4 in. Seal option: John Crane, 1.62 in., T-2, double mechanical seal with pressurized barrier fluid lubrication system. Constructed of ASTM A536 60-40-18 ductile iron. Inlets: (1) 6 in. dia. suction port with an 11 in. dia. flange and (8) 3/4 in. dia. thru holes at a center distance of 3-1/2 in. Outlets: (1) 3 in. dia. suction port with a 7-1/2 in. dia. flange and (4) 3/4 in. dia. thru holes at a center distance of 4 in. Overall dimensions: 2 ft. 8 in. L x 2 ft. 1-1/2 in. W x 1 ft. 8 in. H. (ACN85a)



