

## 1998 Krack Evaporator – 10.45 Tons

**Mfg: Krack**



**Model: PCC2L-336-3-1-DXR22-HGC-LH**

**Stock No: SFEC3264.4**



**Serial No: 493541-01A**


1998 Krack Evaporator. Model: PCC2L-336-3-1-DXR22-HGC-LH. S/N: 493541-01A. Refrigerant: DX R-22. Capacity: 125,400 Btuh @ 10°F TD or 10.45 tons. Coil has copper tubes and aluminum fins (3 FPI). Airflow: 21,600 cfm. (2) 30 in. dia. fans with (2) Baldor fan motors, 1HP each, 1140 rpm, 208-230/460 V, 3.75-3.4/1.7 amps, 60 Hz, 3 phase. Defrost: hot gas coil only, air defrost. Aluminum drain pan with galvanized case and cover. Options include removable legs. Approximate weight 1900 lbs. Inlets: (1) ¾ in. port, (1) 1 in. port. Outlets: (1) 2 in. port, (1) 1 ½ in. drain port. Overall dimensions: 12 ft. 3 in. L x 4 ft. 6 in. W x 4 ft. 10 in. H. (ACN75).











ADDISON, ILL

MODEL PGC21-336-3-1-DXR22-HGC-LH  
 SERIAL NO. 493541-01A  
 MFOR 8/98 INSPECTED 982  
 REFRIGERANT R-22  
 DESIGN PRESSURE 302 PSIG

**MOTOR CIRCUIT**

AMOUNT	VOLTS	HZ	PH	H.P.	EA	FLAEA.
2	460	60	3	1		1.90

MINIMUM CIRCUIT AMPACITY 2.30 AMPS  
 MAXIMUM FUSE/HACR CIRCUIT BREAKER 15.00 AMPS

**HEATER CIRCUIT**

WATTS	VOLTS	HZ	PH	FLA

HEATER CIRCUIT 1  
 HEATER CIRCUIT 2  
 HEATER CIRCUIT 3  
 HEATER CIRCUIT 4

**KRACK MODEL UD**

**BALDOR®**  
 INDUSTRIAL MOTOR

THREE PHASE

CAT. NO. M3156T  
 SPEC. 35B101S260H1  
 FRAME 145T SER. F698  
 H.P. 1 DP  
 VOLTS 208-230/460  
 AMPS 3.75-3.4/1.7  
 R.P.M. 1140  
 HZ 60 PH 3 CLASS B  
 SER. F. 1.15 DES B CODE J  
 NEMA NOM. EFF. 80 % P.F. 72 %  
 RATING 40C AMB-CONT

CONNECTION

LOW VOLTAGE  
 6 5 4  
 9 8 7  
 3 2 1  
 LINE

HIGH VOLTAGE  
 6 5 4  
 9 8 7  
 3 2 1  
 LINE

BALDOR ELECTRIC CO.  
 FT. SMITH, ARK.  
 MFD. IN U.S.A.

**BALDOR®**  
 INDUSTRIAL MOTOR

THREE PHASE

CAT. NO. M3156T  
 SPEC. 35B101S260H1  
 FRAME 145T SER. F698  
 H.P. 1 DP  
 VOLTS 208-230/460  
 AMPS 3.75-3.4/1.7  
 R.P.M. 1140  
 HZ 60 PH 3 CLASS B  
 SER. F. 1.15 DES B CODE J  
 NEMA NOM. EFF. 80 % P.F. 72 %  
 RATING 40C AMB-CONT

CONNECTION

LOW VOLTAGE  
 6 5 4  
 9 8 7  
 3 2 1  
 LINE

HIGH VOLTAGE  
 6 5 4  
 9 8 7  
 3 2 1  
 LINE

BALDOR ELECTRIC CO.  
 FT. SMITH, ARK.  
 MFD. IN U.S.A.

401 SO ROHL  
 ADDISON, ILL

MODEL PGC21-336-3-1-DXR22-HGC-LH  
 SERIAL NO. 493541-01A  
 MFOR 8/98 INSPECTED 982  
 REFRIGERANT R-22  
 DESIGN PRESSURE 302 PSIG

**MOTOR CIRCUIT**

AMOUNT	VOLTS	HZ	PH	H.P.	EA	FLAEA.
2	460	60	3	1		1.90

REFRIGERANT R-22  
 DESIGN PRESSURE 302 PSIG

**MOTOR CIRCUIT**

AMOUNT	VOLTS	HZ	PH	H.P.	EA	FLAEA.
2	460	60	3	1		1.90

MINIMUM CIRCUIT AMPACITY 2.30 AMPS  
 MAXIMUM FUSE/HACR CIRCUIT BREAKER 15.00 AMPS

**HEATER CIRCUIT**

WATTS	VOLTS	HZ	PH	FLA

HEATER CIRCUIT 1  
 HEATER CIRCUIT 2  
 HEATER CIRCUIT 3  
 HEATER CIRCUIT 4