

3M-Matic™ Adjustable Case Sealer System

Mfg: 3M-Matic™

Model: 800AF

Stock No: SFEC3803.7a

Serial No: 2251

3M-Matic™ Adjustable Case Sealer System. Model no. 800AF. Serial no. 2251. Maximum case dimensions: 2 ft. 6 in. L. x 1 ft. 10-1/4 in. W. x 2 ft. 5/8 in. H. Minimum case dimensions: 6 in. L. x 3-5/8 in. W. x 6 in. H. (2) Bodine Electric Company Gear Motors: Type: 34X6BFCI-W2. 1/9(1/6 Max), 83 Rpm, 115 V, 1.4(1.8) A, 60 Hz, 1 Phase. 63 LB.-IN, 20.37:1 Ratio. SMC 3 way valve model no. EVHS4500. SMC Filter Regulator model no. EAW2000. Conveyor dimensions: 6 ft. 1 in. L. x 1 ft. 10 in. W. Infeed/Exit Height: 2 ft. 3/8 in. Min. 2ft. 11-3/8 in. Max. Overall dimensions: 6 ft. 3-1/2 in. L. x 3 ft. 4 in. W. x 5 ft. 10-3/4 in. H.(ACN178).









