

1999 FMC VF Advance Electromagnetic Scale Feeder

Mfg: FMC

Model: EL 2412/08 X70

Stock No. SFEP572.1

Serial No. 806534

1999 FMC VF Advance Electromagnetic Scale Feeder. Model: EL 2412/08 X70. S/N: 806534. F.O: B90924. Operating speed: 663 rpm. Stroke: 0.63 in. (6) Leaf springs. Conveyor dimensions: 107 in. L x 24 in. W x 8 in. H. Digital control box. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 5.5-3.2/1.6 amps, 60 Hz, 3 phase. The VF is a two-mass conveyor that delivers exceptional performance in modular distribution systems and packaging lines. In addition, it is a reliable infeed to weigh scales, color sorters and other processing equipment such as ovens, fryers, and freezers. Conveyor discharge: 12 in. diameter. Overall dimensions: 108 in. L x 44 in. W x 46 in. H.

