

Griffin Stainless Steel Slicer

Mfg: Griffin

Model:

Stock No. SFEP610.2a

Serial No.:

Griffin Stainless Steel Slicer. Unit uses (2) 13 in. circular, rotating cutting knives to cut product. There exists a 1/4 in. gap between cutting knives and the 33 in. dia rotating table. Industry Uniserve Univerter 2 HP AC Inverter Drive, input: 208-230 V, 7.5 amps, 50/60 Hz, 3 phase, output: 3.5-230 V, 7.5 amps. Positions easily by rolling on (4) casters. Baldor Industrial Motor, 3/4 hp, 1725 rpm, 230/460 V, 2.2/1.1 amps, 60 Hz, 3 phase. Ohio Gear Drive, 40 ratio, 43.125 rpm (final). Inlets: (1) 2-1/2 in. W x 3 in. H oval infeed, (3) 6 in. dia. ports. Outlets: (1) 36 in. L x 36 in. W. Overall dimensions: 59-1/2 in. L x 55 in. W x 60 in. H.





