

Klenzade Stainless Steel CIP System- 65 Gallon

Mfg: Klenzade

Model:

Stock No.: SFF315.5

Serial No.:

Klenzade Stainless Steel CIP System- 65 Gallon. Inside straight-wall dimensions: 2 ft. L x 2 ft. 3 in. H. Ampco Centrifugal Pump, Model: 3x2-1/2 ZC2, S/N: AA1307-1-1, capacity: 250 gpm, impeller diameter: 5-1/4 in. Baldor Industrial Motor, 7-1/2 hp, 3450 rpm 230/460 V, 17.6/8.7 amps, 60 Hz, 3 phase. (3) Pneumatic Flow Divert Valves mounted to stainless steel manifold. Inlets: (4) 3/4 in. dia. ports, (1) 2 in. S-line fitting, (1) 18 in. L x 18 in. W (top infeed). Outlets: (1) 2 in. dia. ACME fitting, (1) 2 in. dia. port (overflow), (1) 2 in. dia. port, (2) 2 in. dia. S-line fittings. Overall dimensions: 4 ft. L x 3 ft. 3 in. W x 5 ft. 6 in. H.







