

TAG SHIPMENT: P.O. #96-1214

DO NOT SCALE PRINT WORK TO DIMENSIONS ALL DIMENSION ARE OUTSIDE UNLESS OTHERWISE SPECIFIED

NOTE: THIS UNIT IS NOT DESIGNED TO SUPPORT ANY ADDITIONAL PIPING, VALVES, OR CONTROLS. CAUTION: THIS UNIT IS SHIPPED WITH A NITROGEN PRESSURE OF 25 PSIG. EXERCISE CARE WHEN DISCHARGING PRESSURE.


NOTE: THIS UNIT SKIDDED FOR FORK TRUCK LIFTING. DESIGN PRESSURE: 250 PSI ORIFICE FEED: 4.29 GPM LIQUID @ 4.13 PSI MINIMUM LIQUID FEED PRESSURE REQUIRED ABOVE COIL SUCTION PRESSURE AT LIQUID INLET.

UNIT DATA:
CASING: GALVANIZED SHEET
PAN: GALVANIZED SHEET
INSUL W/ GLV SHEET COVER

FAN DATA:
19,775 CFM AIR @ 0" ESP
(4) 24" DIR DRV PROP FAN
(4) 1/2 HP TEAO1140 RPM 56
FRAME 460-3-60 FAN MOTOR
W/ ATO

PERFORMANCE DATA:
20.5 TONS @ 15°F TD
FEED: FL ; BTM ; R-717
HOT GAS DEFROST - COIL ONLY
40°F ROOM; 25°F COIL
25°F LIQUID MECH PUMPED @ 3:1

FRICK SO# 266452		CUSTOMER PO# -----									
IMECO SO# 9905-1		SCALE: NONE									
DATE: 4-26-96		NO. REQD: 2 LH	WEIGHT: 3,050 LBS								
DRAWN BY: KSK		CHKD BY:	APVD BY:								
CUSTOMER											
<table border="1"> <thead> <tr> <th>LTR</th> <th>DESCRIPTION</th> <th>DATE</th> <th>BY</th> </tr> </thead> <tbody> <tr> <td colspan="4" style="text-align: center;">REVISIONS</td> </tr> </tbody> </table>		LTR	DESCRIPTION	DATE	BY	REVISIONS				FRICK COMPANY DUAL TEMP	
		LTR	DESCRIPTION	DATE	BY						
REVISIONS											
Frigid Coil/Imeco <small>YORK INTERNATIONAL</small>		MODEL USB 35L-466H UNIT COOLER									
		DRAWING NO. B-1692991									
		1/1									



TAG SHIPMENT: P.O. #96-1214

DO NOT SCALE PRINT ALL DIMENSION ARE OUTSIDE WORK TO DIMENSIONS UNLESS OTHERWISE SPECIFIED

NOTE: THIS UNIT IS NOT DESIGNED TO SUPPORT ANY ADDITIONAL PIPING, VALVES, OR CONTROLS. CAUTION: THIS UNIT IS SHIPPED WITH A NITROGEN PRESSURE OF 25 PSIG. EXERCISE CARE WHEN DISCHARGING PRESSURE.

NOTE: THIS UNIT SKIDDED FOR FORK TRUCK LIFTING. DESIGN PRESSURE: 250 PSI ORIFICE FEED: 4.29 GPM LIQUID @ 4.13 PSI MINIMUM LIQUID FEED PRESSURE REQUIRED ABOVE COIL SUCTION PRESSURE AT LIQUID INLET.

UNIT DATA:
 CASING: GALVANIZED STEEL SHEET
 PAN: GALVANIZED STEEL SHEET
 INSUL W/ GLV SHEET COVER

FAN DATA:
 19,775 CFM AIR @ 0" ESP
 (4) 24" DIR DRV PROP FAN
 (4) 1/2 HP TEAO 1140RPM 56
 FRAME 460-3-60 FAN MOTOR
 W/ ATO

PERFORMANCE DATA:
 20.5 TONS @ 15°F TD
 FEED: FL ; BTM; R-717
 HOT GAS DEFROST - COIL ONLY
 40°F ROOM; 25°F COIL
 25°F LIQUID MECH PUMPED @ 3:1

LTR	DESCRIPTION	DATE	BY
REVISIONS			
Frigid Coil/Imeco YORK INTERNATIONAL			

FRICK SO# 266452	CUSTOMER PO# -----
IMECO SO# 9905-1	SCALE: NONE
DATE: 4-25-96	NO. REQD: 3 RH
WEIGHT: 3,050 LBS	
DRAWN BY: KSK	CHKD BY: APVD BY:
CUSTOMER	
FRICK COMPANY DUAL TEMP	
MODEL USB 35L-466H UNIT COOLER	DRAWING NO. B-1692990

