

## Jacketed Stainless Steel Steam Kettle with Scraped Surface Agitator - 50 Gallon

<b>Mfg:</b>	<b>Model:</b>
<b>Stock No. SFF365</b>	<b>Serial No.:</b>

Jacketed Stainless Steel Steam Kettle with Scraped Surface Agitator - 50 Gallon. Inside dimensions: 26 in. dia. x 26 in. H. Shaft diameter: 1-1/2 in. (2) Scrapers: 10 in. L x 5-1/2 in. W. Agitator diameter: 22-1/2 in. Reliance Electric Motor, 1 hp, 1730 rpm, 208-230/460 V, 4.4-4.4/2.2 amps, 60 Hz, 3 phase. Dodge Tigear 2 Speed Reducer, ratio: 60, final speed: 28 rpm, max torque out: 1547 lb-in. Inlets: (1) 26 in. dia. open top, (1) 1 in. dia. FNPT (media). Outlets: (1) 2 in. dia. S-line fitting, (1) 1/2 in. dia. FNPT (media). Overall dimensions: 2 ft. 9 in. L x 2 ft. 5 in. W x 4 ft. 4 in. H.



