

Urschel Dicer

Mfg: Urschel

Model: GK-A

Stock No.: SGM4014.100

Serial No.: 2176

Urschel Dicer. Model: GK-A. S/N: 2176. Maximum product size: 5-1/2 in. (in any dimension). Crosscut knife cut sizes: 1 in. Number of crosscut knives: 6. Knife width: 7 in. Circular knife cut sizes: 3 in. Number of circular knives: 3. Knife diameter: 4 in. The model G, with proper knives, has the capability to produce crinkle cut slices, three-dimensional cuts having four crinkle surfaces, or plain cuts from a variety of fruits and vegetables. Strips can move without interruption across the top surface of the slicing knife holder into the circular knives where they are cut into cubes, or other three-dimensional cuts of a selected size. Electric Apparatus Motor, 2 hp, 1755/1460 rpm, 751/625 rpm (final), 200/208/230/460 V, 5.8-5.5/5.2/2.6 amps, 60/50 Hz, 3 phase. Motor pulley diameter: 3 in. Gear pulley diameter: 7 in. Pulley ratio: 0.428. Inlets: (1) 1 ft. 6-1/2 in. L x 1 ft. 3-1/2 in. W infeed hopper. Outlets: (1) 12 in. L x 7 in. W discharge chute. Overall dimensions: 6 ft 1-3/4 in L x 3 ft 10 in W x 4 ft 1-1/4 in H.







