

Case Conveyor

Mfg:

Model:

Stock No. SGMPB040.2

Serial No.

Case Conveyor. Belt dimensions: 94 in. L x 24 in. W. Product input/output height: 32-1/2. Dayton motor. Dayton motor drive, ratio: 15, maximum input: 1 hp, maximum input rpm: 1750, maximum output torque: 445 in-lbs. 115 V, 50/60 Hz, 1 phase. Dayton control with speed switch. Overall dimensions: 96 in. L x 31 in. W x 34 in. H.

