

Conveyor System Stainless Steel

Mfg:

Model:

Stock No. SGMPB090.3a

Serial No.

Conveyor System. Stainless steel. (3) Reliance Electric motors, 1 hp, 1725 rpm, 208-230/460 V, 2.8-2.8/1.4 amps, 60 Hz, 3 phase. (3) Tigear motor drive, 10 ratio, 172.5 out rpm. Dual belt system. Belt dimensions: 92 in. L x 8 in. W (each one). Belt divider clearance: 10-1/2 in. W. Product input/output height: 37 in. Overall dimensions: 11ft. 7 in. L x 31 in. W x 40 in. H.

