

Safeline Metal Detector W/Conveyor

Mfg: Safeline

Model: PPH/14X06/SS/100-300/HO/V3

Stock No. SGMPB153.31

Serial No. 57457

Safeline Metal Detector w/Conveyor. Model PPH/14X06/SS/100-300/HO/V3. S/N: 57457. REF NO. 19004-01. M/C NO. 333. REF PHASE -02.54, PWR/DR NO. 076, OOBV 520, M/C NO.313, REF PHASE 520, PWR/ DR NO.051 OOBV 00.00. Sensitivity tested with test strips as 1.5 mm ferrous material, 1.5 non-ferrous material, 2.0 mm non-magnetic stainless steel. Actual numbers may vary depending on local site conditions, product tested and other factors. Clearance above belt: 13-3/4 in. W x 4 in. H. Belt: 12 in. W. Detector head without guards: 13-3/4 in. W.; with guards: 12-3/4 in. W. (4) Locking casters. Wheels: 4 in. dia. Stainless all-thread gives about 6 in. of adjustment, and casters will raise the conveyer 6-1/2 in. from its lowest position. (ACN395)



