

## 1994 DCA Stainless steel Gas Fryer

Mfg: DCA

Model: RFG 324 DE

Stock No. SGMT264.9

Serial No. 566

1994 DCA Stainless steel Gas Fryer. Model: RFG 324 DE. S/N: 566. (6) Heat tubes: 24 in. L x 2 in. diameter. 75,000 BTU/Hr rating. Container: 24 in. L x 24 in. W x 7-1/2 in. H. Container oil capacity: 16 gallons for high level, 13.5 gallons for low level. (15) Fryer screens: 23 in. x 23 in. Mesh: 0.20 in. Open flow control: 1/4 in., 1/2 in., 3/4 in. and close. Controls: 120 V, 50/60 Hz, single phase. Portable table dimensions and fryer cover: 30 in. x 29 in. Inlet gas: (1) 1 in. threaded female. Steam outlet: 16-1/2 in. x 3-3/4 in., Overall dimensions: 43 in. L x 31 in. W x 60 in. H.

