

## Capper

Mfg:

Model:

Stock No. SHCA920.4a

Serial No.:

Capper. Capacity: 80 ppm. Maximum product dimensions: 2-1/2 in. W x 6-1/2 in. H. Conveyor length: 37-1/2 in. Star wheel diameter: 10 in. (5) Omron Photoelectric switches also includes control panel with start/stop and emergency disconnect buttons. (4) Adjustable legs. Electrol Conveyor Motor, 1/25 hp, 3450 rpm, 288 rpm (final), 90 V, 0.4 amps, 12:1 ratio, torque 3.9 in.-lb. Star Wheel Motor, 1/27 hp, 400 rpm, 34 rpm (final), 90 V, 0.5 amps, 12:1 ratio, torque: 55 in.-lb. Infeed/exit height: 39 in. Overall dimensions: 37 in. L x 36-1/2 in. W x 56-1/2 in. H.



