

## COP Tank- 100 Gallon

<b>Mfg:</b>	<b>Model:</b>
<b>Stock No. SHCC179. 34</b>	<b>Serial No.</b>

COP Tank- 100 Gallon. 316 stainless steel. Tank features dual manifolds with (18) 1/4 in. dia. spray ports, a Terrice temperature valve with 1/2 in. dia. inlet/outlets, a deep well thermometer, and an Allen-Bradley power box. Reliance Motor: 10 hp, 3510 rpm, 230/460 V, 24/12 amps, 60 Hz, 3 phase. Tri-Clover Centrifugal Pump. Model: C216MD21T-S, S/N: H7770. Inlets/outlets for pump: (2) 1-1/2 in. dia. threaded fittings. Inlets/outlets for tank: (2) 3/4 in. dia. pipes, (1) 2 in. dia. Q-line, (1) 2-1/2 in. dia. drain with strainer. Overall dimensions: 83 in. L x 31 in. W x 87 in. H.



