

Jacketed Paddle Blender

Mfg:

Model:

Stock No.: SHCA433.17

Serial No.:

Jacketed Paddle Blender. Inside dimensions: 1 ft. 3-1/2 in. dia. x 6 ft. 10 in. L. Paddle size: 2 in. L x 2 in. W. Side scraper size: (3) 6 ft. 8 in. L x 2-3/4 in. W. Access doors: (3) 1 ft. 7-1/2 in. L x 11 in. W. Reliance Electric motor, 10 hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Foote-Jones Powertech Gear Drive, 40 rpm (final). Inlets: (1) 3/4 in. dia. NPT (jacket), (1) 9-1/2 in. dia. infeed with a 13-1/2 in. dia. flange. Outlets: (1) 3/4 in. dia. NPT (jacket), (1) 10 in. L x 9 in. W discharge. Overall dimensions: 10 ft. 10-1/2 in. L x 2 ft. 8 in. W x 3 ft. H.





SHAFT MOUNTED DRIVE

SERIAL NUMBER
8004937-01

MODEL NUMBER
7215 F 24

CLASS I RATING
14.8 H.P. 40 RPM

RECOMMENDED LUBRICANT

TEMP.	A.G.M.A.	A.S.T.M.
15°-60°F	3	S-465
50°-125°F	4	S-700

WARNING: FOR SAFETY, THIS UNIT MUST NOT BE OPERATED ABOVE ITS SERVICE RATING.

SHAFT MOUNTED DRIVE

SERIAL NUMBER
8004937-01

MODEL NUMBER
7215 F 24

CLASS I RATING
14.8 H.P. 40 RPM

RECOMMENDED LUBRICANT

TEMP.	A.G.M.A.	A.S.T.M.
15°-60°F	3	S-465
50°-125°F	4	S-700

WARNING: FOR SAFETY, THIS UNIT MUST NOT BE OPERATED ABOVE ITS SERVICE RATING, AND IT MUST BE MAINTAINED AS DESCRIBED IN THE MAINTENANCE MANUAL.

UNIT SHIPPED DRY. FILL TO PROPER LEVEL WITH RECOMMENDED LUBRICANT.

POWERTECH FT
Foote-Jones
DANVERS GROVE, IL 60119
7215 756