

1999 Hughes Company Stainless Steel Drum Cooker

Mfg: Hughes

Model: 004-2326D

Stock No. SHNZ002.

Serial No. 99-19199

1999 Hughes Company Stainless Steel Drum Cooker. Model: 004-2326D. S/N: 99-19199. Product capacity: 6,750 lbs/hr based on 50 lbs/cu. ft. product density. Water capacity 305 gal. Maximum steam pressure: 125 psi. USDA approved, stainless steel construction. Last used as hot hold reel for cooked pasta, this CIP unit features: a rotary blanching reel, open flighted 60 in. dia x 8 ft. L screw with solid and perforated screen sets and includes an internal spray wand, jack screw lift off cover and an overflow skimmer. Reliance Electric Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.4-6.4/3.2 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, 21.51 ratio, 80.19 rpm (final). Inlets: (3) 1-1/2 in. dia. S-line fittings (spray lines). Outlets: (2) 8 in. dia. ports, (1) 27-1/2 in. L x 12 in. W discharge. Overall dimensions: 14 ft. 9 in. L x 101 in. W x 10 ft. H.









